

Hyper Index 1.67 (MR7) Spherical Single Vision Blank

ASAHI-LITE®

Diameter (mm)	Nominal convex curve (D)	Power range at main meridian (D)	Actual convex curve (N=1.53) (D)	Radius of curvature R1 (mm)	Sagitta depth gauge 50mm bell (mm)	Nominal concave curve (N=1.53) (D)	Center thickness (mm)	Edge thickness (mm)
70	0.50 EX	-8.25 to -10.00	0,465	1.140,89	0,274	8,31	5,5	15,2
70	0.50	-7.25 to -8.00	0,465	1.140,89	0,274	7,06	3,3	11,3
80	1.00	-6.25 to -7.00	0,817	648,43	0,482	6,90	2,8	12,6
80	2.00	-4.25 to -6.00	1,614	328,36	0,953	6,90	4,0	12,6
80	3.00	-2.25 to -4.00	2,398	221,00	1,419	6,90	5,3	12,6
80	4.00	0.00 to - 2.00	3,282	161,48	1,947	6,42	4,5	9,7
75	5.00	+0.25 to +1.00	3,567	148,59	2,118	4,80	6,4	8,0
70	6.00	+1.25 to +2.50	4,355	121,70	2,595	6,42	5,3	7,8
70	7.00	+2.75 to +4.00	5,246	101,03	3,142	6,42	6,4	7,8
65	8.00	+4.25 to +6.00	5,882	90,11	3,537	4,80	7,7	6,5
65	10.00	+6.25 to +9.00	8,150	65,03	4,998	4,80	10,2	6,5
65	12.00	+9.25 to +11.00	9,700	54,63	6,055	6,20	10,7	6,5
60	14.00	+11.25 to +14.00	11,260	47,07	7,189	6,20	11,5	6,0
80	7.25	+7.00 to -6.00	6,33	83,7	3,821	6,40	13,0	13,2
80	8.25	+6.00 to -4.75	7,36	72,0	4,480	6,40	13,0	11,3
80	9.25	+5.00 to -3.75	8,24	64,3	5,059	6,40	13,0	9,4