

## 1.60 (MR8) Lenticular Single Vision Blank 68 mm

**ASAHI-LITE®**

Diameter (mm)	Nominal convex curve (D)	Actual convex curve (N=1.530) (D)	Radius of curvature R1 (mm)	Sagitta depth gauge 50 mm bell (mm)	Center thickness (mm)	Edge thickness (mm)
40/68	6.00	6,03	87,89	3,63	10,7	8,0
40/68	8.00	8,03	66,00	4,92	11,6	8,0
40/68	10.00	10,35	51,21	6,52	12,6	8,0
40/68	12.00	12,35	42,91	8,03	13,5	8,0
40/68	14.00	14,20	37,32	9,61	14,2	8,0
40/68	16.00	15,65	33,87	11,02	14,8	8,0
40/68	18.00	17,33	30,58	12,97	15,5	8,0
40/68	20.00	19,50	27,18	16,52	14,2	8,0
40/68	22.00	21,35	24,82	10,12	15,0	8,0

