

1.60 (MR8) Spherical Bifocal Flat Top S28 Blank 70 mm

ASAHI-LITE®

Diameter (mm)	Nominal convex curve (D)	Power range at main meridian (D)	Actual convex curve (N=1.53) (D)	Radius of curvature (mm)	Sagitta depth gauge 50mm bell (mm)	Center thickness (mm)	Edge thickness (mm)	Add. powers in 0.25 D steps (D)
70 / 28	0.50	-10.00 to -5.25	0,52	1019,23	0,31	6,0	13,0	1.00 to 3.50
70 / 28	2.00	-5.00 to -2.00	2,03	261,08	1,20	5,2	10,5	1.00 to 3.50
70 / 28	4.00	-3.00 to -1.00	3,92	135,20	2,33	5,5	8,5	1.00 to 3.50
70 / 28	6.00	-2.00 to +2.00	6,04	87,75	3,64	9,0	8,5	1.00 to 3.50
70 / 28	8.00	+2.00 to +5.00	8,05	65,84	4,93	10,2	7,0	1.00 to 3.50

