

1.60 (MR8) Spherical Bifocal Flat Top S35 Blank 75 mm

ASAHI-LITE®

Diameter (mm)	Nominal convex curve (D)	Power range at main meridian (D)	Actual convex curve (N=1.53) (D)	Radius of curvature (mm)	Sagitta depth gauge 50mm bell (mm)	Center thickness (mm)	Edge thickness (mm)	Add. powers in 0.25 D steps (D)
75 / 35	0.50	-10.00 to -5.25	0,53	1000,00	0,31	5,6	14,0	1.00 to 3.50
75 / 35	2.00	-5.00 to -2.00	2,03	261,08	1,20	4,6	11,0	1.00 to 3.50
75 / 35	4.00	-3.00 to -1.00	3,92	135,20	2,33	5,1	9,0	1.00 to 3.50
75 / 35	6.00	-2.00 to +2.00	6,04	87,75	3,64	7,3	7,0	1.00 to 3.50
75 / 35	8.00	+2.00 to +5.00	8,04	65,92	4,92	10,5	7,0	1.00 to 3.50

