

1.50 Lenticular Single Vision Blank

ASAHI-LITE®

Diameter (mm)	Nominal convex curve (D)	Actual convex curve (N=1.53) (D)	Radius of curvature R1 (mm)	Sagitta depth gauge 50mm bell (mm)	Actual concave curve (N=1.53) (D)	Center thickness (mm)	Edge thickness (mm)
35 / 65	6.00	6,54	81,04	3,953	0,60	8,5	7,5
35 / 65	8.00	8,64	61,34	5,326	0,15	10,0	7,5
35 / 65	10.00	10,46	50,67	6,597	0,15	10,4	7,5
35 / 65	12.00	12,55	42,23	8,195	2,15	13,0	8,0
35 / 65	14.00	14,02	37,80	9,447	2,15	10,0	8,0
35 / 65	16.00	15,75	33,65	11,126	0,60	12,2	8,0
35 / 65	18.00	17,46	30,36	13,138	0,60	13,0	8,0
35 / 65	20.00	19,55	27,11	16,624	0,15	14,2	8,0
35 / 65	22.00	21,21	24,99	10,008	0,65	14,5	8,0
40 / 68	6.00	6,02	88,04	3,624	2,25	11,0	8,0
40 / 68	8.00	8,04	65,92	4,925	2,25	11,6	8,0
40 / 68	10.00	10,37	51,11	6,532	2,25	12,6	8,0
40 / 68	12.00	12,32	43,02	8,010	2,25	13,2	8,0
40 / 68	14.00	14,22	37,27	9,628	2,25	14,2	8,0
40 / 68	16.00	15,70	33,76	11,072	0,65	16,7	8,0
40 / 68	18.00	17,32	30,60	12,955	0,65	17,6	8,0
40 / 68	20.00	18,71	28,33	15,004	0,65	18,3	8,0

