

1.50 Spherical Single Vision Blank 75 mm

ASAHI-LITE®

Diameter (mm)	Nominal convex curve (D)	Power range at main meridian (D)	Actual convex curve (N=1.530) (D)	Radius of curvature R1 (mm)	Sagitta depth gauge 50 mm bell (mm)	Center thickness (mm)	Edge thickness (mm)
75	Plano	-8.00 to -12.00	0,00	26.500,00	0,01	8,5	16,0
75	0.50	-7.00 to -9.00	0,53	1.000,00	0,31	9,0	16,0
75	1.00	-6.50 to -10.50	1,00	530,00	0,59	9,8	16,0
75	2.00	-5.25 to -8.00	1,98	267,68	1,17	11,0	16,0
75	3.00	-4,25 to -6.00	2,98	177,85	1,77	9,2	13,0
75	4.00	-2.25 to -5.00	3,99	132,83	2,37	10,5	13,0
75	5.00	+1.00 to -3.00	5,00	106,00	2,99	12,0	13,0
75	6.00	+2.00 to -2.00	6,02	88,04	3,62	9,0	8,0
75	7.00	+2.00 to +4.00	6,90	76,81	4,18	9,0	7,5
75	8.00	+2.25 to +5.00	8,05	65,84	4,93	11,0	7,0
75	9.00	+4.00 to +7.00	8,92	59,42	5,52	13,0	7,5
75	10.00	+6.00 to +10.00	10,08	52,58	6,32	14,5	7,0