

1.50 Spherical Single Vision Blank 80 mm

ASAHI-LITE®

Diameter (mm)	Nominal convex curve (D)	Power range at main meridian (D)	Actual convex curve (N=1.530) (D)	Radius of curvature R1 (mm)	Sagitta depth gauge 50 mm bell (mm)	Center thickness (mm)	Edge thickness (mm)
80	Plano	-8.00 to -12.00	0,00	26.500,00	0,01	7,2	16,0
80	2.00	-5.25 to -8.00	1,98	267,68	1,17	10,5	16,0
80	4.00	-2.25 to -5.00	3,99	132,83	2,37	10,0	13,0
80	5.25	+1.00 to -3.00	5,27	100,57	3,16	12,5	13,0
80	6.00	+2.00 to -2.00	6,06	87,46	3,65	10,0	10,0
80	7.25	+1.00 to +4.00	7,27	72,90	4,42	11,0	8,0
80	8.00	+2.25 to +5.00	8,04	65,92	4,92	14,0	9,0
80	9.00	-4.00 to +7.00	8,96	59,15	5,54	14,5	8,0
80	10.00	+6.00 to +10.00	10,07	52,63	6,32	16,5	7,0